

# 760251099 | EPX-1U-PNL-OPEN-FX



EPX 1U open fixed panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	EPX

## General Specifications

<b>Application</b>	Accepts three LGX/1000 footprint panels/cassettes   Accepts three PNL-type adapter panels or ReadyPATCH® modules
<b>Color</b>	Black
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Module/Adapter Pack Slots, quantity</b>	3
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Fibers, quantity</b>	72
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	327.91 mm   12.91 in

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	1.179 kg   2.6 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

