

PB-G3T-2



Tapered Pipe Frame Stand-Off Bracket, 36 in, for 2 in to 5 in OD legs

Product Classification

| | |
|----------------------|---|
| Portfolio | CommScope® |
| Product Type | Stand-off mount |
| Ordering Note | CommScope® standard product in the United States and Canada |
| Warranty | One year |

General Specifications

| | |
|--------------------|-------------------------------|
| Mounting | Legs, 50.8–127 mm (2–5 in) OD |
| Tower Taper | Tapered |

Dimensions

| | |
|-----------------------------------|--------------------|
| Height | 1,447.8 mm 57 in |
| Width | 254 mm 10 in |
| Length | 838.2 mm 33 in |
| Mounting Diameter, maximum | 127 mm 5 in |
| Mounting Diameter, minimum | 50.8 mm 2 in |
| Stand-off Distance | 914.4 mm 36 in |

Material Specifications

| | |
|----------------------|--------------------------|
| Material Type | Hot dip galvanized steel |
|----------------------|--------------------------|

Mechanical Specifications

| | |
|--------------------------------|--|
| Wind Rating | 120 mph (BWS) at 150 ft AGL 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC |
| Wind Rating Test Method | TIA/EIA-222 |

PB-G3T-2

Packaging and Weights

| | |
|---------------------------|----------------------|
| Included | Clamps Stand-off |
| Packaging quantity | 1 |
| Weight, net | 62.6 kg 138.009 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

| | |
|--------------------|--|
| Warranty | For more information, please consult our Product Warranty guidelines |
| Wind Rating | BWS—Base Wind Speed; FBC—Florida Building Code |