

RM-SS-L



Ring Mount Tie Back Support Kit

Product Classification

Product Type Ring mount

General Specifications

Mounting Monopole, 762–1524 mm (30–60 in) OD

Sectors, quantity 1

Dimensions

Height 254 mm | 10 in

Width 1,219.2 mm | 48 in

Length 1,219.2 mm | 48 in

Mounting Diameter, maximum 1524 mm | 60 in

Mounting Diameter, minimum 762 mm | 30 in

Mounting Circumference, maximum 4,785.36 mm | 188.4 in

Mounting Circumference, minimum 2,392.68 mm | 94.2 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Angle | Hardware | Mount

Packaging quantity 1

Weight, net 79.4 kg | 175.047 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.andrew.com/ProductCompliance

RM-SS-L

ROHS	Compliant
UK-ROHS	Compliant

