

RM-SS-M



Ring Mount Tie Back Support Kit

Product Classification

Product Type Ring mount

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Sectors, quantity 1

Dimensions

Height 254 mm | 10 in

Width 1,219.2 mm | 48 in

Length 1,219.2 mm | 48 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Mounting Circumference, maximum 3,990.34 mm | 157.1 in

Mounting Circumference, minimum 1,196.34 mm | 47.1 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Angle | Hardware | Mount

Packaging quantity 1

Weight, net 63.5 kg | 139.993 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

RM-SS-M

ROHS

Compliant

UK-ROHS

Compliant

