# 5-600



#### Stand-Off Bracket, 72 in, includes pipe

# **Product Classification**

Product Type Stand-off mount

#### General Specifications

Mounting Straight or tapered legs up to 88.9 mm (3-1/2 in) OD, clamps included

Note One 20 ft omni antenna

Pipe, quantity 1

Tower Taper Non-tapered | Tapered

#### Dimensions

 Height
 812.8 mm | 32 in

 Width
 127 mm | 5 in

 Length
 1,828.8 mm | 72 in

 Pipe Length
 812.8 mm | 32 in


 Pipe Outer Diameter
 48.26 mm | 1.9 in

 Stand-off Distance
 1,828.8 mm | 72 in



# S-600

# Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

# Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL

Wind Rating Test Method TIA/EIA-222

#### Packaging and Weights

Included Clamps | Stand-off

Packaging quantity 1

**Weight, net** 24.5 kg | 54.013 lb

# Regulatory Compliance/Certifications

Agency Classification

ANDREW® an Amphenol company

# S-600

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

