760250899 | OCAB-P-S4-01-IGR-D250xW535



Inground-root for the 72f cabinet, depth 250mm, including mounting hardware

Product Classification

Regional Availability	EMEA
Product Type	Fiber cross-connect hub
Product Series	OCAB

General Specifications

Color	Light Gray (RAL 7035)
Mounting	Cabinet

Dimensions

Height	280 mm	11.024 in
Width	535 mm	21.063 in
Depth	250 mm	9.843 in
Enclosure Size	Small	

Material Specifications

Finish	Powder coated polyester
Material Type	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space	Outdoor, buried
Qualification Standards	IK10

Packaging and Weights

Included	Mounting hardware
Packaging quantity	8
Packaging Type	Pallet

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 25, 2024



760250899 | OCAB-P-S4-01-IGR-D250xW535

Regulatory Compliance/Certifications

Agency

ROHS **UK-ROHS**

Classification

CHINA-ROHS **REACH-SVHC**

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant

Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 25, 2024

