



ION-M4 U AC AI 380-385 390-395 High Power Remote Unit for TETRA Applications

Product Classification

Product Type	Remote unit
Product Brand	ION®-M

General Specifications

Minimum Software Requirement	ION-M SW V8.10.0
Note	Detailed Product Specifications are available. Please contact your local ANDREW representative.
Power Class	High

Electrical Specifications

Impedance	50 ohm
License Band	TETRA
Voltage Range	100 to 240 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	380 – 385 MHz
Wavelength	1550 nm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	390 – 395 MHz
--------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



7773877-0001
