

# SHK-12-3-P



Single Hanger Kit for 1/2 in coaxial cable, triple stack; includes hardware and angle adapter

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	ValuSite™
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Cables per Hanger</b>	3
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	78 mm   3.071 in
<b>Width</b>	25.9 mm   1.02 in
<b>Length</b>	46.2 mm   1.819 in
<b>Compatible Cable Diameter Range</b>	15.2–16.3 mm
<b>Compatible Diameter, maximum</b>	16.3 mm   0.642 in
<b>Compatible Diameter, minimum</b>	15.2 mm   0.598 in
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel 304
----------------------	------------------------------------------

## Mechanical Specifications

# SHK-12-3-P

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

### UV Resistance, minimum with no degradation

≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

### Height, packed

30.4 cm | 11.969 in

### Width, packed

27.9 cm | 10.984 in

### Length, packed

2.5 cm | 0.984 in

### Included

Angle adapter | Hardware

### Packaging quantity

1

### Weight, gross

0.45 kg | 0.992 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power