



ERA® Wireless Communications Switch Subrack, 4 U -48Vdc

This unit does not support CAT6A powered access points.

OBSOLETE

Replaced By:

7844068-02  
WCS-4 DC

ERA® Wireless Communications Switch Subrack, 4 U -48Vdc, with integrated DCDC converter

Product Classification

Product Type	Subrack
Product Brand	ERA®

General Specifications

Mounting	Rack
Note	Detailed Product Specifications are available. Please contact your local ANDREW representative.
Rack Type	EIA 19 in
Slots Available, quantity	19

Dimensions

Height	177 mm   6.969 in
Width	482 mm   18.976 in
Depth	450 mm   17.717 in

Packaging and Weights

Height, packed	522 mm   20.551 in
Width, packed	585 mm   23.032 in
Depth, packed	185 mm   7.283 in
Included	Fan filter   Fan tray

Weight, net10.8 kg | 23.81 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

