

SHK-158-1-P



Single Hanger Kit for 1-5/8 in coaxial cable, single stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	ANDREW® non-standard product

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	1
Height	79 mm 3.11 in
Width	25.9 mm 1.02 in
Length	90.4 mm 3.559 in
Compatible Cable Diameter Range	49–51.1 mm
Compatible Diameter, maximum	50.8 mm 2 in
Compatible Diameter, minimum	49 mm 1.929 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel 304
---------------	--

SHK-158-1-P

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 38.1 cm | 15 in

Width, packed 38.1 cm | 15 in

Length, packed 7.6 cm | 2.992 in

Included Angle adapter | Hardware

Packaging quantity 1

Weight, gross 0.57 kg | 1.257 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power