

# 760250660 | FIST-RSKG-8-SIL



FIST Gel Sealing Kit for round splice closure port, sealing 8 cables with diameter between 3 and 5 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Gel sealing kit
<b>Product Series</b>	FIST-GC02
<b>Ordering Note</b>	Cable jackets containing flame retardant components are advised to be combined with the Silicone gel multi-out seal

## General Specifications

<b>Application</b>	For use with FIST-GC02 Fiber closures
<b>Cable Capacity, maximum</b>	8
<b>Color</b>	Black

## Dimensions

<b>Single Cable Diameter, maximum</b>	5 mm   0.197 in
<b>Single Cable Diameter, minimum</b>	3 mm   0.118 in

## Packaging and Weights

<b>Included</b>	Cable termination brackets   Dummy plugs   Multi-out gel seal
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

# 760250660 | FIST-RSKG-8-SIL

---

UK-ROHS

Compliant/Exempted

