
## 810009939/DB | S-144-LN-8W-M12NS/25G/S



Fiber OSP cable, LightScope® ZWP All-Dielectric Self-Supporting, 144 fiber, 2.5mm Gel-filled Tubes, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series S-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Filler, quantity 0

Jacket Color Black

Jacket Marking Meters

Subunit, quantity 12

Fibers per Subunit, quantity 12

Total Fiber Count 144

Dimensions


**Buffer Tube/Subunit Diameter** 2.5 mm | 0.098 in

**Diameter Over Jacket** 16.28 mm | 0.641 in

Representative Image



# 810009939/DB | S-144-LN-8W-M12NS/25G/S



### Material Specifications

Jacket Material PE

### Mechanical Specifications

Minimum Bend Radius, loaded244 mm9.606 inMinimum Bend Radius, unloaded163 mm6.417 in

**Tensile Load, long and short term**See Sag and Tension tables in Product Documentation section

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

 Impact
 2.94 N-m | 26.021 in lb

 Impact Test Method
 FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Optical Specifications** 

**Fiber Type** G.652.D and G.657.A1 | G.652.D and G.657.A1

**Environmental Specifications** 

Installation temperature  $-30 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Page 2 of 3



# 810009939/DB | S-144-LN-8W-M12NS/25G/S

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards

ANSI/ICEA S-87-640 | IEEE-1222

**Environmental Space** Aerial, self-support

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Drip** 80 °C | 176 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

**Heat Age**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 181 kg/km | 121.626 lb/kft

Included Products

DB-8W-LT - LightScope® ZWP Singlemode

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

