

SSHAK-3812



SnapStak® Hanger Kit for 3/8 in RET cable

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	ANDREW® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	40.9 mm 1.61 in
Width	22.9 mm 0.902 in
Length	66 mm 2.598 in
Compatible Cable Diameter Range	7–9 mm
Compatible Diameter, maximum	9 mm 0.354 in
Compatible Diameter, minimum	7.1 mm 0.28 in
Nominal Size	3/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	EPDM rubber Stainless steel
---------------	-------------------------------

SSHAK-3812

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
--------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight

Packaging and Weights

Height, packed	32.5 cm 12.795 in
Width, packed	13.5 cm 5.315 in
Length, packed	15.5 cm 6.102 in
Packaging quantity	10
Weight, gross	1.4 kg 3.086 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power