


SWH-200-10



PIM-Guard®, SnapWrap Cable Management Strap. Bundle multiple cable types and sizes into a 1/2" (12.7mm) to 2" (50.8mm) bundle with Snap-in installation. Package of 10

- Manage multiple cables in a single universal wrapping strap
- Replaces hangers and endless combinations of multi-cable grommets
- Simpler BOMs, easier standardization
- Optimized to reduce PIM while maximizing structural integrity

Product Classification

Product Type	Cable management
Product Brand	PIM-Guard®
Ordering Note	CommScope® standard product (Global)

General Specifications

Accessories	Hangers
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder
Patent Number	For patents see www.cs-pat.com

Dimensions

Maximum Stack Height	0
Height	34.8 mm 1.37 in
Width	34.8 mm 1.37 in
Length	228.6 mm 9 in
Compatible Cable Diameter Range	12.7–50.8 mm
Compatible Diameter, maximum	50.8 mm 2 in
Compatible Diameter, minimum	12.7 mm 0.5 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

SWH-200-10

Tensile Strength	6,894.76 N/mm ² 1000000 psi
Vibration Survival	≥4 hours at resonant frequency
Wind Speed, survival with 1/2 in (12 mm) radial ice	201.168 km/h 125 mph

Environmental Specifications

Installation temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	5 cm 1.969 in
Width, packed	18 cm 7.087 in
Length, packed	31 cm 12.205 in
Packaging quantity	10
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height	Fiber, Hybrid, Power
Tensile Strength	Tensile Strength at 73° F