

CF141-XXXM-M56

CF141 Jumper with interface types NEX10 Male and NEX10 Male, 0.56 m



Product Classification

Product Type	Braided cable assembly
Product Series	CF141-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CF141-50
Interface, Connector A	NEX10 Male
Interface, Connector B	NEX10 Male
Specification Sheet Revision Level	A

Dimensions

Length	0.56 m 1.837 ft
Nominal Size	0.141 in

Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
100–3000 MHz	1.135	24

Jumper Assembly Sample Label

C141-XMxm-M56

Batch Manufacturing Date (two digit year and week)

Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMScope Andrew Solutions™

F4-DMDM-2M-D — Part Number

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710

Product of UNITED STATES 12US220001242 — Serial Number

