

TT-4310



4.3-10 coupling nut tightening tool

Product Classification

Product Type	Tool
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Application	Torques 4.3-10 connectors
Tool Life	50 connector installations
Tool Type	Tightening tool

Dimensions

Wrench Opening	22.098 mm 0.87 in
-----------------------	---------------------

Material Specifications

Material Type	Plastic
----------------------	---------

Mechanical Specifications

Torque Value	0.33 in lb 0.037 N-m
---------------------	------------------------

Environmental Specifications

Installation temperature	0 °C to +40 °C (+32 °F to +104 °F)
---------------------------------	------------------------------------

Packaging and Weights

Height, packed	96.52 mm 3.8 in
Width, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.08 kg 0.176 lb

Regulatory Compliance/Certifications

TT-4310

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system