

#### Torque Wrench for 1-1/4 in EZfit® connectors, 45 mm

#### **Product Classification**

Product Type Wrench
Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

## General Specifications

**Application** Attaches connectors to coaxial cable

**Calibration** 6 mo

**Tool Type** Torque wrench

#### Dimensions

**Wrench Opening** 44.958 mm | 1.77 in

#### Material Specifications

Material Type Steel

### Mechanical Specifications

**Torque Tolerance** +5/-0

**Torque Value** 504.49 in lb | 57 N-m

#### Packaging and Weights

 Height, packed
 299.72 mm | 11.8 in

 Width, packed
 299.72 mm | 11.8 in

 Length, packed
 106.68 mm | 4.2 in

Packaging quantity 1

**Weight, gross** 2.19 kg | 4.828 lb

## Regulatory Compliance/Certifications

ANDREW®
an Amphenol company

# TW-114-EZFC

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

