

TW-114-EZFC



Torque Wrench for 1-1/4 in EZfit® connectors, 45 mm

Product Classification

Product Type	Wrench
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Application	Attaches connectors to coaxial cable
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening	1.77 in 44.958 mm
-----------------------	---------------------

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	+5/-0
Torque Value	504.49 in lb 57 N-m

Packaging and Weights

Height, packed	11.8 in 299.72 mm
Width, packed	11.8 in 299.72 mm
Length, packed	4.2 in 106.68 mm
Packaging quantity	1
Weight, gross	2.19 kg 4.828 lb

Regulatory Compliance/Certifications

TW-114-EZFC

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

