TW-4310



Torque Wrench for coupling torque of 4.3-10 connectors, 22 mm opening

OBSOLETE

Replaced By:

TW-4310-SP

Slim profile coupling torque wrench for 4.3-10 connectors, 22 mm opening, 8Nm torque

Product Classification

Product Type	Wrench
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Application	Torques 4.3-10 connectors
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening 22.098 mm | 0.87 in

Material Specifications

Material Type Steel

Mechanical Specifications

Torque Tolerance	-0/+2	
Torque Value	44.25 in lb	5 N-m

Packaging and Weights

Height, packed	165 mm	I	6.496 in
Width, packed	145 mm	I	5.709 in

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

TW-4310

Agency

Length, packed	330 mm 12.992 in
Carton Quantity	10
Packaging quantity	1
Weight, gross	0.89 kg 1.962 lb

Regulatory Compliance/Certifications

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025