

# TW-4310

---



Torque Wrench for coupling torque of 4.3-10 connectors, 22 mm opening

## Product Classification

<b>Product Type</b>	Wrench
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Application</b>	Torques 4.3-10 connectors
<b>Calibration</b>	6 mo
<b>Tool Type</b>	Torque wrench

## Dimensions

<b>Wrench Opening</b>	22.098 mm   0.87 in
-----------------------	---------------------

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

## Mechanical Specifications

<b>Torque Tolerance</b>	-0/+2
<b>Torque Value</b>	44.25 in lb   5 N-m

## Packaging and Weights

<b>Height, packed</b>	165 mm   6.496 in
<b>Width, packed</b>	145 mm   5.709 in
<b>Length, packed</b>	330 mm   12.992 in
<b>Carton Quantity</b>	10
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.89 kg   1.962 lb

# TW-4310

---

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system