

# TW-78-EZFC

---



Torque Wrench for 7/8 in EZfit® connectors, 34 mm

## Product Classification

<b>Product Type</b>	Wrench
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Application</b>	Attaches connectors to coaxial cable
<b>Calibration</b>	6 mo
<b>Tool Type</b>	Torque wrench

## Dimensions

<b>Wrench Opening</b>	34.036 mm   1.34 in
-----------------------	---------------------

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

## Mechanical Specifications

<b>Torque Tolerance</b>	+5/-0
<b>Torque Value</b>	300.93 in lb   34.001 N-m

## Packaging and Weights

<b>Height, packed</b>	299.72 mm   11.8 in
<b>Width, packed</b>	299.72 mm   11.8 in
<b>Length, packed</b>	106.68 mm   4.2 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	2.19 kg   4.828 lb

## Regulatory Compliance/Certifications

# TW-78-EZFC

---

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

