



# NOVUX™ Specialty Range Closures

The first modular ecosystem for the networks of today and tomorrow

North America Region

CommScope's new NOVUX™ ecosystem is the next step in the evolution of connectivity and fiber-to-the-X (FTTX) networks. Configurable, scalable and simple, NOVUX transforms networks with a modular, end-to-end architecture.

The NOVUX Specialty Range Closures (SRCs) are a modern drop solution that's ideal for last-mile fiber network applications—both above and below ground. CommScope's advanced Octopus™ gel seal simplifies access and service and protects the closures from harsh conditions.

**COMMScope®**

# Features and benefits

- **Capacity:**
  - Up to 24 fiber splices
  - 1 splitter
  - 4 ports
  - 8 cables (double stacking not to exceed 6.2 mm)
- Accepts round or flat drop cables, or blown fiber tubes
- **Port size:**
  - 1 to 8 mm, 0.04 to 0.32 in round cables
  - 8 x 4.5 mm, 0.32 x 0.18 in flat cables
- Air valve option (via port) with 6 cables (double stacking) *Color: black RAL9005*
- **Security:** Lead wire through eye hole, 4 positions
- **Dimensions:** 267 x 117 x 49 mm, 10.5 x 4.6 x 2 in, with integrated pole mounting features on the back side (length x width x height)
- IP68 2-meter water head, 20kPa
- Tested to IEC 60529

## Ready for the field workforce of the future


We've designed the NOVUX SRCs to be ready for the field, and ready for your workforce. They feature factory-installed hinges and a cover that opens from the bottom. The closures are fast and easy to access, thanks to CommScope's Octopus gel seal technology. A lead wire provides security.

Octopus protects the SRCs from harsh environmental conditions and is extremely comfortable and resilient—even after numerous closure accesses.


## NOVUX: The FTTX ecosystem

NOVUX is engineered from the get-go as a new FTTX system architecture and complete ecosystem with closures and terminals that span the outside plant fiber network—from the trunk and feeder to the distribution and drop. Its modular architecture means that components and accessories are easily configurable to fit each application and are available in high volumes to meet demand.

[LEARN MORE ABOUT NOVUX](#)



# NOVUX Specialty Range Closures ordering information



**\* Cable retention\***

A	None
B	NVX-CR-MC-FT-NN
D	NVX-CR-SA-SM-NN

\* 2 cable attachments are supplied.

**Cable Termination Unit (CTU) options**

 <p><b>NVX-CR-SA-SM-NN</b></p> <ul style="list-style-type: none"> <li>• Round cable</li> <li>• Dia up to 8 mm</li> <li>• Strength member</li> <li>• Aramide yarns</li> <li>• Single layer</li> </ul>	 <p><b>NVX-CR-MC-FT-NN</b></p> <ul style="list-style-type: none"> <li>• Flat cable</li> <li>• Metal clip</li> <li>• Range: 3 x 5 to 4 x 8 mm</li> </ul>
---	---

Configurations available for order		
<p><b>SRC3-U5A1B1BB000</b> MID: 760251022</p> <ul style="list-style-type: none"> <li>• SRC 100, black version, underground</li> <li>• No adapters</li> <li>• Splice only</li> <li>• 12x SMOUV 45 splice</li> <li>• No splitter</li> <li>• 2x NVX-CR-MC-FT-NN cable retention</li> </ul>	<p><b>SRC3-U5A1B1BB001</b> MID: 760251030</p> <ul style="list-style-type: none"> <li>• SRC 100, black version, underground</li> <li>• No adapters</li> <li>• Splice only</li> <li>• 12x SMOUV 45 splice</li> <li>• No splitter</li> <li>• 2x NVX-CR-MC-FT-NN cable retention, including Tone Wire Connector (100/pk 88823Y-000 FDSC-GATOR-TEL-SPLICE)</li> </ul>	<p><b>SRC3-U5A1C1BB000</b> MID: 760251026</p> <ul style="list-style-type: none"> <li>• SRC 100, black version, underground</li> <li>• No adapters</li> <li>• Splice only</li> <li>• 24x SMOUV 45 splice</li> <li>• No splitter</li> <li>• 2x NVX-CR-MC-FT-NN cable retention</li> </ul>

Contact your CommScope representative for configuration availability.

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement. We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realize a better tomorrow. Discover more at [commscope.com](https://commscope.com)

**COMMSCOPE®**

---

[commscope.com](https://commscope.com)

Visit our website or contact your local CommScope representative for more information.

© 2021 CommScope, Inc. All rights reserved.

Unless otherwise noted, all trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability, with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001. Further information regarding CommScope's commitment can be found at [www.commscope.com/corporate-responsibility-and-sustainability](https://www.commscope.com/corporate-responsibility-and-sustainability).

PA-1155211-EN (05/21)