

HFA206-4SNOK6



HELIAX® Hybrid Cable Assembly for Nokia AirScale RRUs. End 1: 4 fibers terminated DLC with R2CT weather shrouds and 6AWG blunt-cut power cord breakout. End 2: 4 fibers terminated DLC and 2-6AWG conductors blunt cut

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	HFA
Ordering Note	CommScope® non-standard product

General Specifications


Conductors, quantity	2
Construction Type	Hybrid standard tail
Interface, Connector A	DLC
Interface Feature, connector A	Uniboot
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Outdoor
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	4

Dimensions

Cable Assembly Length Range (ft)	15 – 150
Diameter Over Jacket	18.31 mm 0.721 in
Center Conductor Gauge	6 AWG

Ordering Tree

HFA206-4SNOK6



Mechanical Specifications

Minimum Bend Radius 221 mm | 8.701 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

Cable weight 0.5 kg/m | 0.336 lb/ft

HFA206-4SNOK6

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)