HFT206-4SNOK6



HELIAX® Hybrid Cable Assembly. HQLC End 1: 4 fibers DLC for Nokia
AirScale RRUs, R2CT with power connector pre-installed (red / black conductors). End 2: 4 fibers terminated LC and 2 X 6 AWG conductors terminated at hybrid trunk connector

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Hybrid cable assembly

Product Brand HELIAX®

Product Series HET

Ordering Note ANDREW® non-standard product

General Specifications

Conductors, quantity 2

Construction Type Hybrid standard tail

Interface, Connector A DLC

Interface Feature, connector A

Uniboot

Interface Body Style, connector A

Straight

Interface, Connector B

HQ-LC

Interface Feature, connector B

Outdoor

Interface Body Style, connector B

Straight

Jacket Color

Black

Total Fibers, quantity 4

Dimensions

Cable Assembly Length Range (ft) 15 – 200


Diameter Over Jacket 18.31 mm | 0.721 in

Center Conductor Gauge 6 AWG

Ordering Tree



HFT206-4SNOK6



Mechanical Specifications

Minimum Bend Radius 221 mm | 8.701 in

Optical Specifications

Fiber Mode Singlemode
Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.75

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Packaging and Weights



HFT206-4SNOK6

Cable weight

0.5 kg/m | 0.336 lb/ft

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

