WB-TK24D



Trapeze Kit, 24 in wide, two rungs

Product Classification

Product Type

Trapeze kit

General Specifications

Application	Waveguide bridge kit, 24 in
Cable Runs, quantity	28
Hole, quantity	24
Mounting	Waveguide bridge channel
Rungs, quantity	1

Dimensions


Height	101.6 mm 4 in
Width	609.6 mm 24 in
Length	152.4 mm 6 in
Hole Size	3/4 in 7/16 in





WB-TK24D

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Threaded rod | Z-bracket

Packaging quantity

5.9 kg | 13.007 lb

Regulatory Compliance/Certifications

1

Agency

Weight, net

Classification

Page 2 of 6



WB-TK24D

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant


Included Products

ZB-H8

 Horizontal Z-bracket, 23 in, for 14 coaxial cable runs



ZB-H8



Horizontal Z-bracket, 23 in, for 14 coaxial cable runs

Product Classification

Product Type Z-Bracket

General Specifications

Cable Runs, quantity	14
Hole, quantity	14
Mounting	Walls


Dimensions

Height	50.8 mm 2 in
Width	152.4 mm 6 in
Length	584.2 mm 23 in
Hole Size	3/4 in 7/16 in

Page 4 of 6



Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included	Z-bracket
Packaging quantity	1
Weight, net	2.4 kg 5.291 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant

Page 5 of 6



ZB-H8



Compliant



Wind Rating

BWS-Base Wind Speed; FBC-Florida Building Code

Page 6 of 6

