
WC-SC12D



Z-bracket, Wall Coaxial Cable Support Covers for SnapStak® Snap-in Hangers, four coaxial cable runs

Product Classification


Product Type	Cover
General Specifications	
Cable Runs, quantity	4
Mounting	Walls
Dimensions	
Height	228.6 mm 9 in
Width	914.4 mm 36 in
Length	2,438.4 mm 96 in

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 19, 2023



Outline Drawing



Material Specifications

Material Type

Galvanized steel

Mechanical Specifications

Wind Rating

For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included	Cover
Packaging quantity	1
Weight, net	57 kg 125.663 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS

Below maximum concentration value

Page 2 of 3



WC-SC12D

ISO 9001:2015

REACH-SVHC





* Footnotes

Wind Rating

Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant

BWS-Base Wind Speed; FBC-Florida Building Code

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 19, 2023

