# RCP-1K4PUE09200



RapidFiber® Termination Panel, 48-Position 1RU, singlemode, LC/UPC to MPO, 92 m

### Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

### General Specifications

**Functionality** Patching

**Body Style** Symmetrical

 Cable Exit Location
 Rear, left side

 Cable Stub Type
 Indoor, microcable

**Color** Putty white

Door Type, front Hinged | Slide latch | Transparant

**Growth Configuration** Fully loaded

Interface, front LC/UPC

Interface, rear MPO

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

**Shelf Movement** Sliding

Total Fibers, quantity 48

Total Ports, quantity 48

**Transmission Standards** IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

**Dimensions** 

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in




# RCP-1K4PUE09200

**Depth** 

381 mm | 15 in

## Ordering Tree



## Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.652.D | G.657.A2/B2

## **Environmental Specifications**



## RCP-1K4PUE09200

**Operating Temperature**  $-5 \,^{\circ}\text{C} \text{ to } +55 \,^{\circ}\text{C} \text{ (+23 °F to +131 °F)}$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

### Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

