



## HFTP-AM Customer premises fiber wall outlet, no pigtails, one SC/APC adapter

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

## Product Classification

<b>Regional Availability</b>	EMEA   North America
<b>Product Type</b>	Outlet
<b>Product Series</b>	HFTP
<b>Minimum Order Quantity</b>	300

## General Specifications

<b>Color</b>	White
<b>Cover Type</b>	Screw-on
<b>Interface Type</b>	SC/APC
<b>Mounting</b>	Wall mount
<b>Total Ports, quantity</b>	1

## Dimensions

<b>Height</b>	105.156 mm   4.14 in
<b>Width</b>	83.058 mm   3.27 in
<b>Depth</b>	25.146 mm   0.99 in

## Material Specifications

<b>Material Type</b>	LSZH Thermoplastic
----------------------	--------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

# 760249280 | HFTP-AM-S201-E

---

**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Environmental Space** Indoor

## Packaging and Weights

**Packaging quantity** 10

## Included Products

760249281 - HFTP-AM Customer premises fiber wall outlet, no pigtail, no  
HFTP-AM-NN00-E adapter