

#### Crossover Angle, 2.38 in to 2.88 in OD

#### **Product Classification**

**Product Type** Mounting kit

## General Specifications

**Tower Taper** Non-tapered

#### **Dimensions**

 Height
 152.4 mm | 6 in

 Width
 152.4 mm | 6 in

 Length
 152.4 mm | 6 in

 Mounting Diameter, maximum
 73.66 mm | 2.9 in

 Mounting Diameter, minimum
 60.96 mm | 2.4 in

#### Material Specifications

Material Type Hot dip galvanized steel

# Packaging and Weights

Included Angle | U-bolts

Packaging quantity 2

**Weight, net** 1.8 kg | 3.968 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



# XA-2030

