

# DFJ-12S320B

---

HELIAX® Discrete, Single Mode 12 fiber LSZH cable, blunt cut to six HMFOC connectors



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Wireless Fiber Cable Assemblies
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	DFJ
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications


<b>Construction Type</b>	Discrete fiber tail   Discrete fiber trunk
<b>Interface, Connector A</b>	HMFOC
<b>Interface Body Style, connector A</b>	Straight
<b>Interface, Connector B</b>	Unterminated
<b>Interface Feature, connector B</b>	Outdoor
<b>Interface Body Style, connector B</b>	Straight
<b>Jacket Color</b>	Black
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Cable Assembly Length Range (ft)</b>	300 – 500
<b>Diameter Over Jacket</b>	6 mm   0.236 in

## Ordering Tree

# DFJ-12S320B



## Optical Specifications

<b>Fiber Type</b>	G.657.A2/B2
<b>Insertion Loss, typical note</b>	Insertion loss is measured at 1310 and 1550 nm
<b>Insertion Loss, typical</b>	0.75

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Outdoor

## Packaging and Weights

<b>Cable weight</b>	37.1 kg/km   24.93 lb/kft
---------------------	---------------------------

# DFJ-12S320B

---

## \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)