

# FGSB-MSHS-H12

---



FiberGuide® Horizontal Straight Section, 4x24in, 12ft Length, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Straight section
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Straight section

## Dimensions

<b>Height</b>	101.6 mm   4 in
<b>Width</b>	609.6 mm   24 in
<b>Length</b>	3,657.6 mm   144 in
<b>System Dimensions</b>	102 mm x 610 mm (4 in x 24 in)

## Material Specifications

<b>Material Type</b>	Engineering Thermoplastic
----------------------	---------------------------

## Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

## Packaging and Weights

<b>Packaging quantity</b>	2
---------------------------	---

# FGSB-MSHS-H12

---

**Weight, net** 5.953 kg | 13.124 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

