


FGS-MSHS-H10



FiberGuide® Horizontal Straight Section, 4x24in, 10ft Length, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Straight section
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Yellow
Orientation	Horizontal
Section Type	Straight section

Dimensions

Height	102 mm 4.016 in
Width	610 mm 24.016 in
Length	3048 mm 120 in
System Dimensions	102 mm x 610 mm (4 in x 24 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Packaging quantity	2
---------------------------	---

FGS-MSHS-H10

Weight, net 5.103 kg | 11.25 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

