

FJ-2S5-OCT



HELIAX® Discrete, 2 single mode fiber, 5 mm armored cable, flexible breakout, LC with uni-boot to LC with uni-boot, variant length

Product Classification

Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	FJ

General Specifications


Construction Type	Direct fiber tail
Interface, Connector A	LC
Interface Body Style, connector A	Straight
Interface, Connector B	LC
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	2

Dimensions

Breakout Length, connector A	0 mm 0 in
Breakout Length, connector B	0 mm 0 in
Cable Assembly Length Range (m)	2 – 100
Diameter Over Jacket	5 mm 0.197 in

Ordering Tree

FJ-2S5-OCT



Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius 70 mm | 2.756 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Environmental Space Outdoor

Packaging and Weights

Cable weight 40 kg/km | 26.879 lb/kft

FJ-2S5-OCT

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)