

700006125 | D-181683



8-to-1 Unit Splitter, for outdoor cable diameter of 0.41 in

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Unit splitter kit
Ordering Note	Order B sealant separately

General Specifications

Color	Black
Compatible Interface	LC LC, keyed SC ST

Dimensions

Height	11.176 mm 0.44 in
Width	26.67 mm 1.05 in
Length	68.58 mm 2.7 in

Material Specifications

Material Type, body	Acrylonitrile butadiene styrene (ABS)
----------------------------	---------------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

Packaging and Weights

Included	Eight unit splitter Split tube seal Syringe
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

700006125 | D-181683

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant

UK-ROHS

Compliant

