



6-to-1 Unit Splitter, for 0.16 in and 0.20 in core tubes

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Unit splitter kit
Ordering Note	Order B sealant separately

General Specifications

Color	Black
Compatible Interface	LC LC, keyed SC ST

Dimensions

Height	8.128 mm 0.32 in
Width	20.32 mm 0.8 in
Length	50.8 mm 2 in

Material Specifications

Material Type, body	Acrylonitrile butadiene styrene (ABS)
----------------------------	---------------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

Packaging and Weights

Included	Six unit splitter Split tube seal Syringe
Packaging quantity	1

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

