

# 760018838

---



12 Fiber Breakout Kit, loose tube, 900  $\mu\text{m}$

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber breakout kit, rectangular

## General Specifications

<b>Color</b>	Black
<b>Compatible Interface</b>	LC   LC, keyed   SC   ST

## Dimensions

<b>Height</b>	7.62 mm   0.3 in
<b>Width</b>	17.78 mm   0.7 in
<b>Length</b>	43.18 mm   1.7 in
<b>Tube Length</b>	609.6 mm   24 in
<b>Tube Inner Diameter</b>	500 $\mu\text{m}$
<b>Tube Outer Diameter</b>	900 $\mu\text{m}$

## Material Specifications

<b>Material Type, body</b>	Acrylonitrile butadiene styrene (ABS)
<b>Material Type, tubing</b>	Thermoplastic elastomer (TPE)

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Included</b>	Breakout unit   Instruction sheet   Snap together housing   Twelve buffer tubes, 24 in x 900 $\mu\text{m}$
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

