760252499 | MDU-TAP-18-NN/NN



Multi Dwelling unit Terminal access point with SC-APC shuttered connectors, splitter 1:8

- Extremely small form reduces space requirments needed within the building
- Different tap ratio's allows networks to be optimized to reduce loss and improve reach
- Pre-installed splitters protected and sealed
- Suitable for in-building environment
- Utilizes shuttered SC/APC adapters providing a safe working environment
- In-molded color coded label for identification of tap ratio with possiblility of an QR code
- Optional cable attachment for strength relief and aditional cover for the adapters/connectors
- Plug and play solution allows for reduced installation skill requirments and greatly improves speed of installation

Product Classification

Product Type	MDU tap

General Specifications

Functionality	Patching Splitting
Adapter Type	Input (1) Output (8)
Adapters, quantity	9
Color	Light gray
Distribution Type	8-port tap
Interface	SC/APC
Mounting	Wall
Split Ratio	Terminating
Dimensions	

Height	100 mm 3.937 in
Width	75 mm 2.953 in
Depth	60 mm 2.362 in

Ordering Tree

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 20, 2023



760252499 | MDU-TAP-18-NN/NN

MDU-TAP-18-XX/XX

Tap/Thru Split Ratio %	
	NN/NN
	50/50
	60/40
	70/30
	80/20
	85/15
	90/10

Material Specifications

Material Type

Acrylonitrile butadiene styrene (ABS)

Optical Performance

Identification color	Tap/Thru split ratio %	Drop port attenuation (insertion loss) median (dB)	Drop port attenuation (insertion loss) max (dB)	Thru port attenuation (insertion loss) max (dB)
Violet	Terminating	9,50	10,50	NA
Orange	50/50	13,90	14,90	4,10
Red	60/40	14,32	15,32	2,73
Blue	70/30	15,51	16,51	2,22
White	80/20	17,25	18,25	1,25
Yellow	85/15	19,79	20,79	1,13
Green	90/10	20,54	21,54	0,73

Optical Specifications

Fiber Mode

Singlemode

Environmental Specifications

Environmental Space	Indoor	I	Riser
Flammability Rating	UL 94 V	-0	

Packaging and Weights

Height, packed	120 mm 4.724 in
Width, packed	170 mm 6.693 in
Depth, packed	295 mm 11.614 in
Packaging quantity	8
Packaging Type	Box Carton

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 20, 2023

