

# HCCO-1ADDLOA

---



EHD-1U Pre-stubbed Patch Panel with LC/UPC Adapter and 144f I/O, Riser/LSZH rollable ribbon cable, right cable entry, singlemode with cable length in meters from 25m to 400m in 25m increments

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	EHD

## General Specifications

<b>Color</b>	Black
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stub tail
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	144

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	465.84 mm   18.34 in
<b>Cable Length</b>	25 m   82.021 ft

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2   OS2
<b>Insertion Loss, maximum</b>	0.35 dB

## Environmental Specifications

<b>Safety Standard</b>	UL 60950
------------------------	----------

# HCCO-1ADDLOA

---

## Included Products

- 760239307  
N-144-CN-RR-F12YL/8G1/99G  
/C – Fiber indoor cable, All-Dielectric, LSZH, Riser-Rated, Gel-Free, Central Tube Rollable Ribbon, 144 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Cca flame rating