

CMD/CSAPAE615V500



Power Adapter for Subscriber Amplifiers, CMD, ac/dc, 15 V, 500 mA, EISA VI

OBSOLETE

Product Classification

Product Type	RF amplifier power adapter
Product Brand	HomeConnect®

General Specifications

Plug Type	Type A
-----------	--------

Electrical Specifications

Input Current, maximum	190 mA
Input Voltage, specific	100-240 Vac @ 50-60 Hz
Output Load Regulation Tolerance, maximum	±5%
Output Power, maximum	7.5 W
Output Voltage Ripple, maximum	150 mVpp
Inrush Current, maximum	30 A
Operating Current at Voltage	500 mA @ 15 Vdc

Environmental Specifications

Energy Efficiency Standard	EISA 2016, Level 6
Safety Standard	c-UL-us

Packaging and Weights

Height, packed	360.68 mm 14.2 in
----------------	---------------------

CMD/CSAPAE615V500

Width, packed	304.8 mm 12 in
Length, packed	594.36 mm 23.4 in
Carton Quantity	100
Weight, gross	11.34 kg 25 lb