
BLK-RLBT-A01060



Fiber Optic Ribbon Breakout Kit, 12F/ribbon, 72F/tube, 1 tube/leg

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber breakout kit, rectangular
Product Series	BLK-R

General Specifications

Application	For use with ribbon fiber cables
Breakout Legs, quantity	б
Fibers per Ribbon, maximum	12
Fibers per Tube, maximum	72
Tube Type	Ribbon in loose buffer tube
Tubes per Leg, quantity	1
—	

Dimensions

Tube Length	5,001.26 mm	196.9 in
-------------	-------------	----------

Environmental Specifications

Environmental Space

Outdoor

Packaging and Weights

Packaging quantity	1		
Packaging Type	Bag		Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 10, 2023



BLK-RLBT-A01060



Compliant



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 10, 2023

