# UHXMPMXAK

**Base Product** 



Ultra Low Loss (ULL) Multimode OM4 MPO12 (Unpinned) to MPO12 (Pinned), Armored Pre-terminated Trunk Cable, 72-Fiber, Plenum

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

### General Specifications

Connector A, quantity 6

Color, boot A Black

Color, connector A Aqua

Connector B, quantity 6

Color, boot B Black
Color, connector B Aqua

Construction Type Armored | Stranded

Furcation Color Aqua

Interface, Connector A MPO-12/UPC Female

Interface Feature, connector A Unpinned

Interface, Connector B MPO-12/UPC Male

Interface Feature, connector BPinnedJacket ColorAqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 72

**Dimensions** 




# **UHXMPMXAK**

33 in **Breakout Length** 

3 - 999 Cable Assembly Length Range (m)

Cable Assembly Length Range (ft) 10 - 999

### Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Multimode

OM4, LazrSPEED® Fiber Type

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Plenum

#### Included Products

P-072-MZ-5K-F12AQ

Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with 760119834

plenum jacket, Multimode OM4, 72 fiber multi-unit with 12 fiber subunits, gel-free, Feet jacket

marking, Aqua jacket color

MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm 860366210

MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm 860366228

**COMMSCOPE®**