UHXMXUCAM

Base Product



Ultra Low Loss (ULL) Multimode OM4 MPO12 (Pinned) to Unconnectorized, Armored Pre-terminated Trunk Cable, 144-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Connector A, quantity

Color, boot A

Black

Color, connector A

Connector B, quantity

Color, boot B

Black

Color, connector B

Aqua

Construction Type Armored | Stranded

Furcation Color Aqua

Interface, Connector A MPO-12/UPC Male

Interface Feature, connector A Pinned

Interface, Connector B Unterminated

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 144


Dimensions

COMMSCOPE®

UHXMXUCAM

33 in **Breakout Length** Cable Assembly Length Range (m) 3 - 999Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Included Products

Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with 760120048 P-144-MZ-5K-F12AQ

plenum jacket, Multimode OM4, 144 fiber multi-unit with 12 fiber subunits, gel-free, Feet jacket

marking, Aqua jacket color

MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm 860366228

COMMSCOPE®