UHGMPMXAL

Base Product



Ultra Low Loss (ULL) Singlemode MPO12 (Unpinned) to MPO12 (Pinned), Armored Pre-terminated Trunk Cable, 96-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly
Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Connector A, quantity 8

Color, boot A Black
Color, connector A Green

Connector B, quantity 8

Color, boot BBlackColor, connector BGreen

Construction Type Armored | Stranded

Furcation Color Yellow

Interface, Connector A MPO-12/APC Female

Interface Feature, connector A Unpinned

Interface, Connector B MPO-12/APC Male

Interface Feature, connector BPinnedJacket ColorYellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 96




UHGMPMXAL

Dimensions

Breakout Length 33 in Cable Assembly Length Range (m) 3 - 999Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

-10 °C to +60 °C (+14 °F to +140 °F) **Operating Temperature**

Environmental Space Indoor | Plenum

Included Products

Fiber indoor cable, Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 96 760245034 P-096-MZ-8G1-F12YL

fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking,

Yellow jacket color

MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm 860638317

Page 2 of 3

UHGMPMXAL

860638318

- MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm

