

760252850 | 20" Pole Base 4G/5G, Round



Round 20 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Pole top concealment module for LAA/CBRS radio mounting
- Concealment integrates AC load center/OVP and disconnect

Radio Bracket Mounting Kits ordered separately:

- MTM1193-1101-AMK-E – Ericsson Radio Bracket Kit
- MTM1193-1101-AMK-N – Nokia Radio Bracket Kit
- MTM1193-1101-AMK-S – Samsung Radio Bracket Kit

Product Classification

Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERG
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Co 6005) Metallic Silver Umbra Grey (RAL 7022)
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting
Cooling	Fan Cooling
Power Supply Compatibility	6304 ABB CC1600 DELTA 2.0 PSU-AC-08
Radio Compatibility, Ericsson	1281 220x 440x 4415 4426 4449 4467 4478 6701 6705 8843 8800 Distribution
Radio Compatibility, Nokia	AHFB AHFIB AHIB AWHHF AZQC AZRB Airscale micro Diplexer Power Distrib
Radio Compatibility Samsung	AT1K01 AT1K02 DELTA 2.0 Diplexer Power Distribution RF4402D-D1A RF4437D

Page 1 of 2

760252850 | 20" Pole Base 4G/5G, Round

48A | RT8808-77A

Radios Included None

Dimensions

Height 3,048 mm | 120 in

Height Note 10 ft tall Equipment Base

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Width 508 mm | 20 in

Depth 508 mm | 20 in

Depth Note Round

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487