

NG4-CMDMOR2



NG4access® Cabled Module, singlemode LC/APC to stub, 24 fiber, Rollable Ribbon, Plenum

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber cabled module
Product Brand	NG4access®
Product Series	LSX NG4
Ordering Note	For fiber modules with custom cable lengths, please contact your local CommScope representative

General Specifications


Configuration Type	NG4 Module to Stub tail
Adapters, quantity, front	24
Adapters, quantity, rear	1
Body Style	Straight orientation
Cable Color	Yellow
Cable Type	Plenum - Rollable Ribbon
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/APC
Interface, rear	Stub tail
Polarity	Pairs, straight
Total Fibers, quantity	24

Dimensions

NG4-CMDMOR2

Height	13.3 mm 0.524 in
Width	159.9 mm 6.295 in
Depth	101 mm 3.976 in

Ordering Tree



*** Use XXX for non-standard lengths in meters
Contact CommScope's Technical Assistance Center for availability of other upjacketing options.

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2

Environmental Specifications

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
----------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---