# SRC3-U5A1B1BE000



NOVUX<sup>™</sup> Specialty Range Closure 100, splice only, no adapters, no splitters, 12 splices, SMOUV<sup>®</sup> 45mm splice protectors, black, 2x NVX-CR-TI-SM-NN cable retention

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

#### Product Classification

Regional Availability	Asia   EMEA   Latin America   North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SRC100
General Specifications	
Cable Capacity, Drop	4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in)   4 Round 1.2-8.0 mm (0.05-0.31 in)
Cable Ports Quantity, total	4 multi-out ports (8 cables)
Cable Sealing Type	Compressed gel
Cable Termination Attachments, quantity	2
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Handhole   Partially buried   Pedestal   Wall/Pole Mount, mounting kit included
Network Area Type	Drop
Port Type	No adapter   No adapter
Port, quantity	0
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink

Page 1 of 4


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 17, 2024



# SRC3-U5A1B1BE000

Splicing Capacity, maximum	12
Splicing Capacity, Single Fusion, maximum	12
Splicing Type, Supported Single fusion	
Splitter Type No splitter	
Splitter, quantity	0
Dimensions	
Height	267 mm   10.512 in
Width	117 mm   4.606 in
Depth	49 mm   1.929 in
Cable Entry Drop Port Diameter	8 mm (0.31 in) mm

## Ordering Tree



Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 17, 2024



# SRC3-U5A1B1BE000

#### Material Specifications Material Type Impact-resistant polymer **Optical Specifications** Fiber Type G.652.D | G.657.A1 | G.657.A2 | G.657.B3 **Environmental Specifications Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F) **Environmental Space** Above ground | Below ground | Direct burial **Qualification Standards** IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G **UV Resistance** UV stabilized Water Resistance Flash test valve at 2 psi (20 kPa) Packaging and Weights **Packaging quantity** 10 **Packaging Type** Box | Carton Regulatory Compliance/Certifications Classification Agency ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

NVX-CR-TI-SM-NN

NOVUX™ Cable Termination Unit (CTU) for round cables up to 8 mm diameter, with aramide yearns, single layer

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 17, 2024



# NVX-CR-TI-SM-NN



NOVUX<sup>™</sup> Cable Termination Unit (CTU) for round cables up to 8 mm diameter, with aramide yearns, single layer

### Product Classification

Asia   EMEA   Latin America   North America
Cable termination kit
NOVUX™
CSC

### General Specifications

Application	For use with CSC Fiber closures
Color	Black

### Packaging and Weights

Packaging quantity	20	
Packaging Type	Bag	Box

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

