



FDC Fiber access terminal for aerial applications, 5 mm drop cable rubber sealing, no Adapters, 72 fusion splices

Product Classification

Regional Availability	EMEA Latin America Middle East/Africa North America
Product Type	Single-ended, rectangular fiber closure
Product Series	FDC

General Specifications

Cable Ports Quantity, total	4 round ports + 8 round ports
Cable Sealing Type	Compressed rubber
Closure Sealing Type	Hinged with latch Hinged with latch, bolts and rubber H seal
Closure Style	Single-ended
Color	Black
Mounting	Facade Strand Wall
Port Type	No adapter
Port, quantity	8
Splice Tray Included, quantity	3
Splice Tray Type Included	24-way, heat shrink
Splitter Type	No splitter
Splitter, quantity	0

Dimensions

Height	76.5 mm 3.012 in
Width	237 mm 9.331 in
Length	285 mm 11.22 in
Cable Entry Drop Port Diameter	5 mm (0.20 in) mm
Cable Entry Main Port Diameter	6 mm (0.24 in) mm
Main Cable Diameter, maximum	14 mm 0.551 in

Material Specifications

Material Type Rugged polymer

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

