MPJ2DBBGNN5M

HELIAX® Modular Remote Radio Head Power Cable Assembly, 2 conductors Black/Blue 10mm², Blunt Cut to OEC GEN; CPR rated Cca sl, dl, al. 5 Meter

Product Classification

Regional Availability Asia | EMEA | North America

Portfolio CommScope®

Product Type Power cable assembly

Product Brand HELIAX®
Product Series Modular

Ordering Note CommScope® standard product (Global)

General Specifications

Cable Type Power

Conductors, quantity 2

Construction Type Non-armored

Jacket Color Black

Dimensions

Cord Length 5 m | 16.404 ft


Diameter Over Dielectric4.724 mm | 0.186 inDiameter Over Jacket, nominal16.789 mm | 0.661 in

Center Conductor Gauge 10 mm²

Ordering Tree



MPJ2DBBGNN5M



Material Specifications

Dielectric Material PVC

Filler Material Polypropylene

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius 156 mm | 6.142 in

Cable Retention Strength, maximum 90 N (OEC GEN)

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Environmental SpaceUV resistant for outdoor and/or direct burial installations

Flame Test Method CMP
Flammability Rating CMP

