760252332 | PPL-DM-8U-8LC-0M4-BEU



Propel ULL Multimode OM4 MPO-08 Distribution Module, 4 duplex LC to 1X8f MPO/UPC non-pinned, Method B Enhanced

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 2 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber module

Product Brand Propel
Product Series PPL

General Specifications

FunctionalityBreakoutColor, frontAquaColor, rearGrayInterface, frontLC/UPC

Interface Feature, front Internal shutters

Interface, rear MPO

Interface Feature, rear Internal shutters | Key up/up | Standard | Unpinned

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 8

Total Ports, quantity, front 4

Total Ports, quantity, rear 1

Dimensions

 Height
 11 mm | 0.433 in

 Width
 65 mm | 2.559 in

 Depth
 170 mm | 6.693 in

Optical Specifications

COMMSC PE°

760252332 | PPL-DM-8U-8LC-0M4-BEU

Fiber Mode Multimode

Fiber Type OM4

Insertion Loss, maximum 0.35 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL 62368

Packaging and Weights

Packaging quantity 1

Weight, net 0.109 kg | 0.24 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ROHS Compliant UK-ROHS Compliant

