760242985 | OCM8-SP122LLG-20DB



OCM8 Fiber Optic Splitter Module, Planar, 2x2 Splitter, singlemode, LC /APC, symmetrical split ratio, 2 m pigtails

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Product Type Splitter module

Product Series OCM8

General Specifications

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Distribution Type 2 x 2 splitter

Interface, InputLC/APCInterface, OutputLC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

 Height
 5 mm | 0.197 in

 Depth
 45 mm | 1.772 in

Length 100 mm | 3.937 in

Pigtail Length, Input $2 \, \mathrm{m}$ | $6.562 \, \mathrm{ft}$ Pigtail Length, Output $2 \, \mathrm{m}$ | $6.562 \, \mathrm{ft}$

Pigtail Diameter, Input1.8 mm | 0.071 in

Pigtail Diameter, Output 1.8 mm | 0.071 in

Optical Specifications

Fiber Type G.657.A1

Directivity, minimum 55 dB

Polarization Dependent Loss, maximum 0.3 dB

COMMSC PE°

760242985 | OCM8-SP122LLG-20DB

Uniformity, maximum 1.45 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum4.7 dBReturn Loss, Connector, minimum55 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 1

